



## Triplex Oil-Less Scroll Laboratory Air System

### System Description:

The *Global Vac & Air* Oil-less Scroll Laboratory air system is built as two skids bolted together for ease of transport and installation. One skid consists of the system control panel and three oil-less scroll compressors mounted on an assembled frame in a vertical configuration. The second skid is built with a vertical receiver and two heatless regenerative desiccant drying systems piped in parallel. The system is completely tested before shipment and is built with a single point connection for air discharge, drainage, and system power. The complete assembly is finished in GLOBALVAC white. The system is piped, wired and factory tested prior to shipment.

### Oil-Less Scroll Compressor Assembly:

The system includes three air cooled oil-less scroll compressors rated for continuous duty. Each compressor is belt driven and requires absolutely no oil. All interconnecting wiring, plumbing, and vibrations isolation pads are included. Each assembly contains:

- TEFC NEMA Electric motor
- Integral cooling fan and aftercooler
- 5-micron inlet filter with polyester element
- Exhaust high temperature switch
- Inlet & outlet flex connector
- Adjustable motor mounting base to achieve proper belt tensioning

### Air Filtration, Dryer, and Regulator:

The system contains two heatless regenerative desiccant dryers piped in parallel. Each dryer is sized for full system demand producing a pressure dewpoint of -40°F. Each dryer has an energy savings feature that actuates the purge cycle as needed depending on the actual dew point reading. All filters and the tank drain are manifolded together with an electrically actuated automated drain valve for single point connection of oil-free condensate drainage. Each dryer can independently be isolated without stopping airflow to the facility. Each dryer assembly includes the following items:

- Outlet adjustable pressure regulator with gauge and safety relief valve
- Outlet particulate filter with manual drain and element change indicator
- Inlet filtration consists of two coalescing filters, rated 1 micron and 0.01 micron.

- Outlet filtration consists of one 0.01-micron coalescing filter.

### Air Receiver:

The ASME coded vertical air receiver is ASME coded and rated for a minimum of 200 PSIG. The receiver is epoxy lined for corrosion resistance. Additional receiver size options available. The receiver assembly is equipped with the following items:

- Sight glass to check for excess liquid
- Electrically actuated timer drain valve
- Manual drain valve
- Mechanical water separator between each compressor outlet and tank inlet
- 3-valve bypass
- Pressure Gauge

### Triplex Control Panel:

The system is controlled by a UL labeled duplex mounted and wired control panel.

The control panel is built with:

- Finger safe power distribution block
- 120V control transformer with CB protection for primary and secondary circuits
- 120vac/24vdc power supply
- 7" color OIT with integrated Hand/Off/Auto
- Door mounted system disconnect
- Door mounted Emergency Stop button
- Adjustable run-on timer (frequent start protection) integrated into OIT
- 4-20 mA dew point transmitter with unique autocalibration function and  $\pm 2^{\circ}\text{C}$  accuracy
- 4-20 mA pressure transmitter to control pumps via PLC input
- Selectable, Auto Timed Alternation (default), Auto Alternation or Manual Alternation
- Hour meter integrated into OIT
- Dry contacts for remote monitoring
- Maintenance screens with adjustable time intervals for tracking critical maintenance items
- UL508A listed NEMA 12 enclosure
- Low pressure alarm which may be enabled/disabled
- Door mounted Bypass circuit with selector switch
- Panel mounted pressure gauge
- Ethernet bulkhead for temporary site connection
- *OPTIONAL: Protocol converter for BMS interface (Modbus TCP/IP-BACnet/IP Client Gateway)*



**Triplex Oil-Less Scroll  
Laboratory Air System**

<b>Model Number*</b>	<b>Pump motor rating (HP)</b>	<b>Maximum Pressure (PSIG)</b>	<b>System capacity @ 145 PSIG (SCFM)**</b>	<b>Receiver / Orientation</b>
CH05T-XXL-12V	5	145	38.7	120 Gallon Vertical
CH05T-XXL-20V	5	145	38.7	200 Gallon Vertical
CH07T-XXL-12V	7.5	145	51.6	120 Gallon Vertical
CH07T-XXL-20V	7.5	145	51.6	200 Gallon Vertical
CH10T-XXL-12V	10	145	74.1	120 Gallon Vertical
CH10T-XXL-20V	10	145	74.1	200 Gallon Vertical
CH10T-XXL-24V	10	145	74.1	240 Gallon Vertical

\*XX in the model number is a placeholder for system voltage. 43=460V/3/60Hz, 23=230V/3/60Hz, 53=575V/3/60Hz

\*\* All data shown assumes 60 Hz electrical supply